


# Alternative Wrist Technology

TRS Nylon



Disconnect



FM

Friction Disconnect



Wedgrip



Flex Wrists



Disconnect adapters for Fillauer®-HOSMER® Wrists



## Wrist Components

### TRS Nylon Wrists

MODEL:	STYLE	SIZE	PRODUCT CODE	SPECIFICATIONS
<i>Infant</i>	Round	Very Small	<i>INFANTWRIST</i>	1.25 in. D. (3.2 cm. D.)
<i>Child</i>	Round	Small	<i>TRS CHILDWRIST</i>	1.5 in. D. (3.8 cm. D.)

### Fillauer®-Hosmer® Nylon Capp®

MODEL:	STYLE	SIZE	PRODUCT CODE	SPECIFICATIONS
<i>CAPP®</i>	Round	Small	<i>WH 55108</i>	1.5 in. D. (3.8 cm. D.)
	Round	Medium	<i>WH 55109</i>	1.75 in. D. (4.4 cm. D.)

### Fillauer®-Hosmer® Wrists

MODEL:	STYLE	SIZE	PRODUCT CODE	SPECIFICATIONS
<i>Wedgrip</i>	Round	Large	<i>WH 61897</i>	2 in. D. (5 cm. D.)
	Round	Medium	<i>WH 62351</i>	1.75 in. D. (4.4 cm. D.)
	Oval	Large	<i>WH61970</i>	2.25 in. x 1.6 in. (5.7 cm x 4.1 cm.)
	Oval	Medium	<i>WH 62354</i>	2 in. x 1.55 in. (5.1 cm x 4 cm.)
<i>Disconnect</i>	Round	Large	<i>WH 61862</i>	2 in. D. (5 cm. D.)
	Round	Medium	<i>WH 62342</i>	1.75 in. D. (4.4 cm. D.)
	Oval	Large	<i>WH 61922</i>	2.25 in. x 1.6 in. (5.7 cm. x 4.1 cm.)
	Oval	Medium	<i>WH 62343</i>	2 in. x 1.55 in. (5.1 cm. x 4 cm.)
<b>TRS Improved Insert</b>			<b>QDA6H</b>	
<i>FM Disconnect</i>	Round	Large	<i>WH 58297</i>	2 in. D. (5 cm. D.)
	<b>Insert</b>		<b>WHI 51052</b>	
<i>Friction/Disconnect</i>	Round	Large	<i>WH 58152</i>	2 in. D. (5 cm. D.)
	Round	Medium	<i>WH 58151</i>	1.75 in. D. (4.4 cm. D.)
	Oval	Large	<i>WH 58150</i>	2.25 in. x 1.63 in. (5.7 cm. x 4.1 cm. D.)
	<b>Insert</b>		<b>WHI 58153</b>	
<i>Flexion</i>	Round	Large	<i>WH 51100</i>	2 in. D. (5 cm. D.)
	Round	Medium	<i>WH 51084</i>	1.75 in. D. (4.4 cm. D.)